

LINE SÄÄNTELYVIRANOMAISTEN LH.V-L 200-10-10



- Säädin - Yksiportainen
- Asennus putkiston tai kaasun paneeli
- Sopivat puhtaat kaasut ja seokset, ei syövyttävä
- Kromattua messinkiä

Laboratoriot ja analyysit

Domains of applications

LH-säätimet on suunniteltu putkiverkoston kaasun syöttämiseen matalapaineiseen putkistoon korkeapainelähteestä.

Designed for implementation of:

Syövyttämättömät puhtaita kaasuja jopa N60 lukien Alphagaz™ 1 & 2, Ei-syövyttäviä seoksia pitoisuus on suurempi kuin 1 ppm

Specifications

Maximal inlet pressure at 15°C 200 bar
Outlet Pressure 1 to 10 bar
Nominal nitrogen flow 2 Nm³/h*
Set pressure 16 bar

Materials


Body Kromi messinkipäällysteinen

Safety Alert

⚠ Varoitus! Jos käytetään palavien kaasujen, kaikki tyhjennys- ja ylivuoto venttiilit on kerättävä.

Dimensions

Net weight : 1 kg



Operating instructions

OP 250 - LH.V-L

Connection

Inlet connection: 1 sisäänmenoaukko Ø 16 x 1,336 SI naaras






Outlet connection: 2 pakoaukkojen G 3/8 BSPP naaras





Relief valve connection: Op-Brass puristusliitin 6mm, Brass Puristusholkit

Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
152885	REG LH 200-10-10 V	seokset	200 bar	10 bar	10 Nm ³ /h	Ø 16x1.336 SI-kirjain	G 3/8 BSPP naaras	Messinki

Options

	Product Number	Long designation
	16516	CONN. G3/8 BSPP M NIP. F/PIPE Ø 4-6MM
	16521	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 1/8" OD Brass *Flat seal PTCFE
	16522	CONNECTION G 3/8" Male Compression Fitting 6 MM Br
	16523	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 1/4" OD Brass *Flat seal PTCFE
	16524	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 10mm OD Brass *Flat seal PTCFE
	16526	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 8mm OD Brass *Flat seal PTCFE
	16558	Connector SS G3/8 BSPP Male *Compression fitting 6mm OD SS *Flat seal PTCFE
	16562	COMP. FITTING G3/8" 8 MM SS

	Product Number	Long designation
	16564	CONNECTION G 3/8 BSPP Male - CF 3/8" - Stainless S
	16566	Connector SS G3/8 BSPP Male *Compression fitting 1/8" OD SS *Flat seal PTCFE
	16567	Connector SS G3/8 BSPP Male *Compression fitting 10mm OD SS *Flat seal PTCFE
	16569	Connector SS G3/8 BSPP Male *Compression fitting 12mm OD SS *Flat seal PTCFE
	19286	Liitäntä G3/8 BSPP M NIP. Ø 8-10MM BR