

CONNECTOR

QLIXBI CONNECTOR S300



- Instant click-on connector saves time and effort.
- You can change over cylinders in seconds
- slogan_type_de_gaz_53

hitsaus, teollinen prosessi

Domains of applications

Designed for:

Argon and Argon inert mixture

Except:

Oxidizing and flammable mixtures are excluded

Specifications

Maximal inlet pressure at 15°C.....300 bar

Käyttölämpötila: -20 ° C + 65 ° C: ssa.

Materials

Body Brass CW617N

Seat PA 6.6

Filter sintrattu pronssi

Seal EPDM EP851

Safety Alert

🔗 alert_securite_27

Dimensions

Length (L) : 101 mm

Height (H) : 197 mm

Depth (D) : 160 mm

Net weight : 1.43 kg



Products

| Product Number | Short Designation | Inlet Fitting | Outlet Fitting | Material |
|----------------|-------------------|---------------|------------------------|----------|
| 203014 | | Qlixbi HPP3 | ISO 5145 Nr.30 (W30x2) | Messinki |