

LINE SÄÄNTELYVIRANOMAISTEN DACC 25-8-12



- Line säädin - Yksiportainen
- Asennus putkiston tai kaasun paneeli
- Sopivat puhtaat kaasut
- Kromattua messinkiä

Laboratoriot ja analyysit, teollinen prosessi

Domains of applications

DACC-säätimet on suunniteltu sovelluksiin, joissa tarvitaan toista vaihetta suurilla virtausnopeuksilla.

Designed for implementation of:

Syövyttämättömät puhtaita kaasuja jopa N60 lukien Alphagaz™ 1 & 2, Ei-syövyttäviä seoksia pitoisuus on suurempi kuin 1 ppm

Except:

Hiilidioksidi

Specifications

Maximal inlet pressure at 15°C 25 bar

Outlet Pressure 0,5 to 8 bar

Nominal nitrogen flow 12 Nm³/h*

Imurointi mahdollista satunnaista puhdistusta varten, Sisäinen/ulkoisen vuotoonopeus ≤ 3x10⁻⁷ mbar.l/s Heliumia, Käyttölämpötila: -20 °C + 50 °C: ssa.

* Nimellinen typen virtauksen 15 °C: ssa.

Materials

Body Kromi messinkipäällysteinen

Seat Messinki

Tasapainoinen venttiili messinki

Main valve NBR päällystetty

Diaphragm Ruostumaton teräs

Kupari metalliseos mekanismi, Ø

Pressure gauge 50mm, Seal PA 6.6

Seal NBR, PA 6.6

Dimensions

Length (L) : 45 mm
 Height (H) : 97 mm
 Depth (D) : 83 mm
 Ø1 : 50 mm
 Net weight : 0.5 kg




Operating instructions

OP 250 - DACC

Connection

Inlet connection: 1 tuloaukon G 3/8 BSPP naaras
 Outlet connection: 1 poistoaukon G 3/8 BSPP naaras

Flow curve



Products




Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
15873	REG DACC 25-8-12	Muut CnHm, seokset	25 bar	8 bar	12 Nm³/h	G 3/8 BSPP naaras	G 3/8 BSPP naaras	Messinki
15874	REG DACC 25-8-12 CF 6MM - CF 6MM	Muut CnHm, seokset	25 bar	8 bar	12 Nm³/h	CF 6mm	CF 6mm	Messinki
7976	REG DACC 25-8-12 CF 10MM - CF 10MM	Muut CnHm, seokset	25 bar	8 bar	12 Nm³/h	CF 10mm	CF 10mm	Messinki
15875	REG DACC 25-8-12 SW 10MM - SW 10MM	Muut CnHm, seokset	25 bar	8 bar	12 Nm³/h	SW 10mm	SW 10mm	Messinki
87866	REG DACC 25-8-12 G3/8 AL M	Muut CnHm, seokset	25 bar	8 bar	12 Nm³/h	G 3/8" BSPP M	G 3/8 BSPP naaras	Messinki

Options

	Product Number	Long designation
	16516	CONN. G3/8 BSPP M NIP. F/PIPE Ø 4-6MM
	16521	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 1/8" OD Brass *Flat seal PTFE

	Product Number	Long designation
	16522	CONNECTION G 3/8" Male Compression Fitting 6 MM Br
	16523	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 1/4" OD Brass *Flat seal PTFE

	Product Number	Long designation
	16524	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 10mm OD Brass *Flat seal PTCFE
	16526	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 8mm OD Brass *Flat seal PTCFE
	16558	Connector SS G3/8 BSPP Male *Compression fitting 6mm OD SS *Flat seal PTCFE
	16562	COMP. FITTING G3/8" 8 MM SS
	16564	CONNECTION G 3/8 BSPP Male - CF 3/8" - Stainless S

	Product Number	Long designation
	16566	Connector SS G3/8 BSPP Male *Compression fitting 1/8" OD SS *Flat seal PTCFE
	16567	Connector SS G3/8 BSPP Male *Compression fitting 10mm OD SS *Flat seal PTCFE
	16569	Connector SS G3/8 BSPP Male *Compression fitting 12mm OD SS *Flat seal PTCFE
	19286	Liitäntä G3/8 BSPP M NIP. Ø 8-10MM BR

Spare parts

Product Number	SP Number	Long designation
15873	16001	Painemittari -1+8+12 bar Ø50 pysty M10x1
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
15874	16001	Painemittari -1+8+12 bar Ø50 pysty M10x1
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
7976	16001	Painemittari -1+8+12 bar Ø50 pysty M10x1
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
15875	16001	Painemittari -1+8+12 bar Ø50 pysty M10x1
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
87866	16001	Painemittari -1+8+12 bar Ø50 pysty M10x1
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8