

LINE SÄÄNTELYVIRANOMAISTEN DACC.S 25-8-12 PHARMA



- Line säädin - Yksiportainen
- Asennus putkiston tai kaasun paneeli
- Soveltuu PHARGALIS kaasujen
- Valmistettu ruostumattomasta teräksestä

Apteekki

Domains of applications

DACC.S PHARMA -säätimet ovat osa laitevalikoimaa, joka on räätälöity lääketeollisuuden vaatimuksiin ja erityisesti farmaseuttisten kaasujen käsittelyyn.

Designed for implementation of:
PHARGALIS™ kaasut

Specifications

Maximal inlet pressure at 15°C 25 bar

Outlet Pressure 0,5 to 8 bar

Nominal nitrogen flow 12 Nm³/h*

Sisäinen/ulkoinen vuotoonopeus ≤ 3x10⁻⁷ mbar.l/s Heliumia, Käyttölämpötila: -20 °C + 50 °C:ssa.

* Nimellinen typen virtauksen 15 °C:ssa.

Materials


Body 316 ruostumatonta terästä

Seat 316L ruostumattomasta teräksestä

Main valve Tasapainoinen venttiili 316L ruostumattomasta teräksestä FKM pinnoitettu

Dimensions

Length (L) : 62 mm
Height (H) : 125 mm
Depth (D) : 83 mm
Ø1 : 50 mm
Net weight : 0.5 kg



Operating instructions

OP 250 - DACC.S

Connection

Inlet connection: 1 tuloaukon G 3/8 BSPP naaras

Outlet connection: 1 poistoaukon G 3/8 BSPP naaras

Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
150289	REG DACC.S PHARMA 25-8-12	Puhtaat kaasut	25 bar	8 bar	12 Nm³/h	G 3/8 BSPP naaras	G 3/8 BSPP naaras	Ruostumaton teräs

Options

	Product Number	Long designation
	16558	Connector SS G3/8 BSPP Male *Compression fitting 6mm OD SS *Flat seal PTCFE
	16562	COMP. FITTING G3/8" 8 MM SS
	16564	CONNECTION G 3/8 BSPP Male - CF 3/8" - Stainless S

	Product Number	Long designation
	16566	Connector SS G3/8 BSPP Male *Compression fitting 1/8" OD SS *Flat seal PTCFE
	16567	Connector SS G3/8 BSPP Male *Compression fitting 10mm OD SS *Flat seal PTCFE
	16569	Connector SS G3/8 BSPP Male *Compression fitting 12mm OD SS *Flat seal PTCFE

Spare parts

Product Number	SP Number	Long designation
150289	15986	PRESSURE GAUGE (-1) - 12 Bar Ø 50mm S.Steel - Lat
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8