


Dimensions

- Length (L) : 120 mm
- Height (H) : 120 mm
- Depth (D) : 158 mm
- Ø1 : 50 mm
- Ø2 : 68 mm
- Net weight : 2.6 kg




Operating instructions

OP 150 - DLM

Connection

- Inlet connection:** HP sylinteri mukaisen liittimen kaasun
- Outlet connection:** 2 pakoaukkojen G 3/8 BSPP naaras
- Relief valve connection:** Op-Brass puristusliitin 6mm, Brass Puristusholkit

Flow curve








Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
155898	REG DLM 300 200-15-50 DIN 6 - CF 6MM	CO2, O2	200 bar	15 bar	50 Nm³/h	DIN 477-1 Nr. 6	CF 6mm	Op-Brass
155896	REG DLM 300 200-15-50 DIN 1 - CF 6MM	H2	200 bar	15 bar	50 Nm³/h	DIN 477-1 Nr. 1	CF 6mm	Op-Brass
155900	REG DLM 300 200-15-50 DIN 10 - CF 6MM	He, N2, Ar	200 bar	15 bar	50 Nm³/h	DIN 477-1 Nr. 10	CF 6mm	Op-Brass
193523	REG DLM 300 200-15-50 DIN 6	CO2, O2	200 bar	15 bar	50 Nm³/h	DIN 477-1 Nr. 6	G 3/8 BSPP naaras	Op-Brass
193522	REG DLM 300 200-15-50 DIN 1	H2	200 bar	15 bar	50 Nm³/h	DIN 477-1 Nr. 1	G 3/8 BSPP naaras	Op-Brass
193524	REG DLM 300 200-15-50 DIN 10	He, N2, Ar	200 bar	15 bar	50 Nm³/h	DIN 477-1 Nr. 10	G 3/8 BSPP naaras	Op-Brass

Options

	Product Number	Long designation		Product Number	Long designation
	16516	CONN. G3/8 BSPP M NIP. F/PIPE Ø 4-6MM		16522	CONNECTION G 3/8" Male Compression Fitting 6 MM Br
	16521	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 1/8" OD Brass *Flat seal PTFE		16523	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 1/4" OD Brass *Flat seal PTFE

	Product Number	Long designation
	16524	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 10mm OD Brass *Flat seal PTCFE
	16526	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 8mm OD Brass *Flat seal PTCFE
	16532	Connector SS G3/8 BSPP Male *Kit N°2 CF 1/8" and 6mm OD SS *Flat seal PTCFE
	16558	Connector SS G3/8 BSPP Male *Compression fitting 6mm OD SS *Flat seal PTCFE
	16562	COMP. FITTING G3/8" 8 MM SS
	16564	CONNECTION G 3/8 BSPP Male - CF 3/8" - Stainless S

	Product Number	Long designation
	16566	Connector SS G3/8 BSPP Male *Compression fitting 1/8" OD SS *Flat seal PTCFE
	16567	Connector SS G3/8 BSPP Male *Compression fitting 10mm OD SS *Flat seal PTCFE
	16569	Connector SS G3/8 BSPP Male *Compression fitting 12mm OD SS *Flat seal PTCFE
	19207	LEAK DETECTOR "1000 BULLES"
	19286	Liitäntä G3/8 BSPP M NIP. Ø 8-10MM BR

Spare parts

Product Number	SP Number	Long designation
155898	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
	18552	PRESSURE GAUGE 0-25 Bar Ø 50mm Vertical Entry G1/4
	167800	KIT of Seals flat PA 6.6 for manometer M10x1 (2 s
155896	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
	17203	FLAT SEAL in PTCFE 18x11,8x2 for inlet connection
	18552	PRESSURE GAUGE 0-25 Bar Ø 50mm Vertical Entry G1/4
	167800	KIT of Seals flat PA 6.6 for manometer M10x1 (2 s
155900	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
	18552	PRESSURE GAUGE 0-25 Bar Ø 50mm Vertical Entry G1/4
	29053	FLAT SEAL in PA 6.6 20x12x2
	167800	KIT of Seals flat PA 6.6 for manometer M10x1 (2 s
193523	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
	18552	PRESSURE GAUGE 0-25 Bar Ø 50mm Vertical Entry G1/4
	167800	KIT of Seals flat PA 6.6 for manometer M10x1 (2 s
193522	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
	17203	FLAT SEAL in PTCFE 18x11,8x2 for inlet connection
	29053	FLAT SEAL in PA 6.6 20x12x2
	167800	KIT of Seals flat PA 6.6 for manometer M10x1 (2 s
193524	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8

Product Number	SP Number	Long designation
193524	18552	PRESSURE GAUGE 0-25 Bar Ø 50mm Vertical Entry G1/4
	29053	FLAT SEAL in PA 6.6 20x12x2
	167800	KIT of Seals flat PA 6.6 for manometer M10x1 (2 s