


Dimensions

Length (L) : 120 mm
Height (H) : 120 mm
Depth (D) : 158 mm
Ø1 : 50 mm
Ø2 : 68 mm
Net weight : 2.6 kg




Operating instructions

OP 150 - DLM

Connection

Inlet connection: HP sylinteri mukaisen liittimen kaasun
Outlet connection: 2 pakoaukkojen G 3/8 BSPP naaras
Relief valve connection: Op-Brass puristusliitin 6mm, Brass Puristusholkit

Flow curve









Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Inlet Fitting Form	Outlet Fitting	Material
181840	REG DLM 300-15-50 ISO5145 N°32-CF 6MM O2	O2	300 bar	15 bar	50 Nm³/h	ISO 5145 N: o 32	Käsi Cr-Brass	CF 6mm	Op-Brass
181841	REG DLM 300-15-50 ISO5145 N°30-CF 6MM NG	He, N2, Ar	300 bar	15 bar	50 Nm³/h	ISO 5145 N: o 30	Käsi Cr-Brass	CF 6mm	Op-Brass
181842	REG DLM 300-15-50 ISO5145 N°38-CF 6MM H2	H2	300 bar	15 bar	50 Nm³/h	ISO 5145 N: o 38	Käsi Cr-Brass	CF 6mm	Op-Brass

Options

	Product Number	Long designation		Product Number	Long designation
	16516	CONN. G3/8 BSPP M NIP. F/PIPE Ø 4-6MM		16524	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 10mm OD Brass *Flat seal PTCFE
	16521	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 1/8" OD Brass *Flat seal PTCFE		16526	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 8mm OD Brass *Flat seal PTCFE
	16522	CONNECTION G 3/8" Male Compression Fitting 6 MM Br		16532	Connector SS G3/8 BSPP Male *Kit N°2 CF 1/8" and 6mm OD SS *Flat seal PTCFE
	16523	Connector Cr-Brass G3/8 BSPP Male *Compression fitting 1/4" OD Brass *Flat seal PTCFE		16558	Connector SS G3/8 BSPP Male *Compression fitting 6mm OD SS *Flat seal PTCFE

	Product Number	Long designation
	16562	COMP. FITTING G3/8" 8 MM SS
	16564	CONNECTION G 3/8 BSPP Male - CF 3/8" - Stainless S
	16566	Connector SS G3/8 BSPP Male *Compression fitting 1/8" OD SS *Flat seal PTCFE
	16567	Connector SS G3/8 BSPP Male *Compression fitting 10mm OD SS *Flat seal PTCFE

	Product Number	Long designation
	16569	Connector SS G3/8 BSPP Male *Compression fitting 12mm OD SS *Flat seal PTCFE
	19207	LEAK DETECTOR "1000 BULLES"
	19286	Liitäntä G3/8 BSPP M NIP, Ø 8-10MM BR

Spare parts

Product Number	SP Number	Long designation
181840	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
	18552	PRESSURE GAUGE 0-25 Bar Ø 50mm Vertical Entry G1/4
	129592	O-RING 7,65 X 1,78; EPDM (FOR 300BAR)
	167800	KIT of Seals flat PA 6.6 for manometer M10x1 (2 s
181841	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
	18552	PRESSURE GAUGE 0-25 Bar Ø 50mm Vertical Entry G1/4
	129592	O-RING 7,65 X 1,78; EPDM (FOR 300BAR)
	167800	KIT of Seals flat PA 6.6 for manometer M10x1 (2 s
181842	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
	18552	PRESSURE GAUGE 0-25 Bar Ø 50mm Vertical Entry G1/4
	129592	O-RING 7,65 X 1,78; EPDM (FOR 300BAR)
	167800	KIT of Seals flat PA 6.6 for manometer M10x1 (2 s