

LINE SÄÄNTELYVIRANOMAISTEN DACC.S 25-8-12



- Line säädin - Yksiportainen
- Asennus putkiston tai kaasun paneeli
- Sopivat puhtaat kaasut
- Valmistettu ruostumattomasta teräksestä

Laboratoriot ja analyysit

Domains of applications

DACC-säätimet on suunniteltu sovelluksiin, joissa tarvitaan toista vaihetta suurilla virtausnopeuksilla.

Designed for implementation of:

Syövyttämättömät puhtaita kaasuja jopa N60 lukien Alphagaz™ 1 & 2, Ei-syövyttäviä seoksia pitoisuus on suurempi kuin 1 ppm

Except:

Typpioksidit

Specifications

Maximal inlet pressure at 15°C 25 bar

Outlet Pressure 0,5 to 8 bar

Nominal nitrogen flow 12 Nm³/h*

Imurointi mahdollista satunnaista puhdistusta varten, Sisäinen/ulkoisen vuotoonopeus ≤ 3x10⁻⁷ mbar.l/s Heliumia, Käyttölämpötila: -20 °C + 50 °C:ssa.

* Nimellinen typen virtauksen 15 °C:ssa.

Materials

Body	316 ruostumatonta terästä
Seat	316L ruostumattomasta teräksestä
Main valve.....	Tasapainoinen venttiili 316L ruostumattomasta teräksestä FKM
Diaphragm	pinnoitettu Hastelloy C®
Pressure gauge	Ruostumaton teräs mekanismi, Ø 50mm
Seal	PCTFE, FKM

Dimensions

Length (L) : 62 mm
 Height (H) : 125 mm
 Depth (D) : 83 mm
 Ø1 : 50 mm
 Net weight : 0.5 kg



Operating instructions

OP 250 - DACC.S




Connection




Inlet connection: 1 tuloaukon G 3/8 BSPP naaras
 Outlet connection: 1 poistoaukon G 3/8 BSPP naaras

Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
15876	REG DACC.S 25-8-12	seokset	25 bar	8 bar	12 Nm ³ /h	G 3/8 BSPP naaras	G 3/8 BSPP naaras	Ruostumatonta teräs
15877	REG DACC.S 25-8-12 CF 6MM - CF 6MM	seokset	25 bar	8 bar	12 Nm ³ /h	CF 6mm	CF 6mm	Ruostumatonta teräs
15878	REG DACC.S 25-8-12 CF 10MM - CF 10MM	seokset	25 bar	8 bar	12 Nm ³ /h	CF 10mm	CF 10mm	Ruostumatonta teräs
87844	REG DACC.S 25-8-12 G3/8 AL M - CF 10MM	seokset	25 bar	8 bar	12 Nm ³ /h	G 3/8" BSPP M	CF 10mm	Ruostumatonta teräs
87847	REG DACC.S 25-8-12 G3/8 AL M	seokset	25 bar	8 bar	12 Nm ³ /h	G 3/8" BSPP M	G 3/8 BSPP naaras	Ruostumatonta teräs

Options

	Product Number	Long designation
	16558	Connector SS G3/8 BSPP Male *Compression fitting 6mm OD SS *Flat seal PTFE
	16562	COMP. FITTING G3/8" 8 MM SS
	16564	CONNECTION G 3/8 BSPP Male - CF 3/8" - Stainless S

	Product Number	Long designation
	16566	Connector SS G3/8 BSPP Male *Compression fitting 1/8" OD SS *Flat seal PTFE
	16567	Connector SS G3/8 BSPP Male *Compression fitting 10mm OD SS *Flat seal PTFE
	16569	Connector SS G3/8 BSPP Male *Compression fitting 12mm OD SS *Flat seal PTFE

Spare parts

Product Number	SP Number	Long designation
15876	15986	PRESSURE GAUGE (-1) - 12 Bar Ø 50mm S.Steel - Lat
	17141	FLAT SEAL in PTFE 14,5x10x2 for outlet port G3/8

Product Number	SP Number	Long designation
15877	15986	PRESSURE GAUGE (-1) - 12 Bar Ø 50mm S.Steel - Lat
	17141	FLAT SEAL in PTFE 14,5x10x2 for outlet port G3/8

Product Number	SP Number	Long designation
15878	15986	PRESSURE GAUGE (-1) - 12 Bar Ø 50mm S.Steel - Lat
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
87844	15986	PRESSURE GAUGE (-1) - 12 Bar Ø 50mm S.Steel - Lat
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
87847	15986	PRESSURE GAUGE (-1) - 12 Bar Ø 50mm S.Steel - Lat
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8