

VAIHDOKSIA ECOGAZ SA 200-50/40-160



- Jatkuva kaasun jakelujärjestelmä putkistossa
- KytKentä 2x1 tai 2x2 200 bar sylintereitä tai nippujen
- Sopiva teolliseen kaasujen
- Messinkiä

Laser, teollinen prosessi

Domains of applications

Designed for implementation of:
teollisuuskaasut

Except:
hiilivedyt

Specifications

Maximal inlet pressure at 15°C 200 bar
 Outlet Pressure 50 bar
 Preset outlet pressure/service first
 stage 50 / 40 bar
 Nominal nitrogen flow 160 Nm³/h*
 Set pressure 80 bar

Sisäinen / ulkoinen vuotomäärä ≤ 10⁻⁸ mbar.l / s., Käyttölämpötila: -20 °C + 50 °C:ssa.

*Takuu enimmäislähtöpaineella P2 enintään tulopaineeseen P3 = 2P2 + 1 bar.

Materials

Panel Laajennus siirtyminen paneeli:
 Frame Ruostumaton teräs
 Regulator Jaloteräspallon 304L, Elin messin-
 ki, messinki mäntä, PA 6.6 istuin
 Pressure gauge Ruostumaton teräs tapaukses-
 sa Ø 50mm, Kupari metalliseos
 mekanismi
 Relief valve Brass yhdistettävissä
 Seal AGS Pb, Delrin[™], EPDM, PA 6.6

INFO +


3.1 Certificate available on demand. Please contact Warehouse team before ordering.

Safety Alert

⚠ Varoitus! Jos käytetään palavien kaasujen, kaikki tyhjennys- ja ylivuoto venttiilit on kerättävä.

Dimensions

Length (L) : 530 mm
Height (H) : 115 mm
Depth (D) : 120 mm
Net weight : 16.3 kg



Operating instructions

OP 310 - ECOGAZ

Connection

Inlet connection: 4 tuloaukkojen +4 toisia vaihtoehtoja Ø 16 x 1,336 SI naispuolinen
Outlet connection: 1 poistoaukon + 2 porttia kerätä puhdistus G 3/8 BSPP naaras
Relief valve connection: Poistoaukon: G 3/8 BSPP F

Products

Product Number	Short Designation	Gas	Inlet Pressure	Outlet Pressure	Flow	Inlet Fitting	Outlet Fitting	Material
178204	MAN ECOGAZ SA 200-50/40-160NG-AR-CO2ExHe	ilma, CO2, N2, Ar	200 bar	50 bar	160 Nm³/h	Ø 16x1.336 SI-kirjain	G 3/8 BSPP naaras	Messinki
155093	ECOGAZ SA 200-50/40-160 H2	H2	200 bar	50 bar	160 Nm³/h	Ø 16x1.336 SI-kirjain	G 3/8 BSPP naaras	Messinki
179176	MAN ECOGAZ SA 200-50/40-160 He	He	200 bar	50 bar	160 Nm³/h	Ø 16x1.336 SI-kirjain	G 3/8 BSPP naaras	Messinki
155092	ECOGAZ SA 200-50/40-160 O2-N2O	N2O, O2	200 bar	50 bar	160 Nm³/h	Ø 16x1.336 SI-kirjain	G 3/8 BSPP naaras	Messinki
147163	MAN ECOGAZ SA 200-50/40-160	inerttikaasuja, H2, O2	200 bar	50 bar	160 Nm³/h	Ø 16x1.336 SI-kirjain	G 3/8 BSPP naaras	Messinki

Options

	Product Number	Long designation
	19331	FITTING AF + FILTER ECOGAZ M20x1,5
	64595	KIT FITTINGS ECOGAZ/M2D G3/8 BSP-G1/2BST
	151865	Connection KIT for purges and relief valve for Man
	152663	KIT Panel Change procedure for cylinders or bundle
	153687	HAZARD Multilingual Panel O2-N2O

	Product Number	Long designation
	153689	HAZARD PANEL NEUTRAL GASES
	155103	HAZARD PANEL FLAMABLE GASES
	155758	KIT CALIBRETED ORIFICE Ø 2,8 PA 6.6 - N2 ECOGAZ 50

Spare parts

Product Number	SP Number	Long designation
178204	15970	Painemittari 0- 200/315 Bar Ø 50mm Sivusuunnassa M10x1 Brass-Cr
	17129	O-RING in EPDM R6 7,2x1,9 mm EP851 (set of 10)
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
	18546	Painemittari 0 -100 Bar Ø 50mm Takaisinsyöttö G1/4 vaihtventtiileille ECOGAZ (paitsi C2H2)
	18884	RELIEF VALVE ECOGAZ Calibrated 50 Bar for Manifold
	19329	Blind Plug for orifice Ø16x1,336 SI Brass
	19403	BLOC VALVE PURGE for Change Overs and Panels ECOGA
	64595	KIT FITTINGS ECOGAZ/M2D G3/8 BSP-G1/2BST
	151862	FLAT SEAL in PA 6.6 for GAUGE Inlet G1/4
	167800	KIT of Seals flat PA 6.6 for manometer M10x1 (2 s
	175874	RELIEF VALVE ECOGAZ Body Brass / EPDM Tightness Pr
	175886	KIT SPARE REGULATOR left for Man ECOGAZ SA 200-50/
	175887	KIT SPARE REGULATOR right for Man ECOGAZ SA 200-50
155093	15970	Painemittari 0- 200/315 Bar Ø 50mm Sivusuunnassa M10x1 Brass-Cr
	17129	O-RING in EPDM R6 7,2x1,9 mm EP851 (set of 10)
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
	18546	Painemittari 0 -100 Bar Ø 50mm Takaisinsyöttö G1/4 vaihtventtiileille ECOGAZ (paitsi C2H2)
	18884	RELIEF VALVE ECOGAZ Calibrated 50 Bar for Manifold
	19329	Blind Plug for orifice Ø16x1,336 SI Brass
	19331	FITTING AF + FILTER ECOGAZ M20x1,5
	19403	BLOC VALVE PURGE for Change Overs and Panels ECOGA
	64595	KIT FITTINGS ECOGAZ/M2D G3/8 BSP-G1/2BST
	151862	FLAT SEAL in PA 6.6 for GAUGE Inlet G1/4
	151865	Connection KIT for purges and relief valve for Man
	155747	KIT CALIBRETED ORIFICE Ø 1,4 PA 6.6 - H2 ECOGAZ 50 Bar - KIT = 3
	167800	KIT of Seals flat PA 6.6 for manometer M10x1 (2 s
	175874	RELIEF VALVE ECOGAZ Body Brass / EPDM Tightness Pr
	175886	KIT SPARE REGULATOR left for Man ECOGAZ SA 200-50/
	175887	KIT SPARE REGULATOR right for Man ECOGAZ SA 200-50
179176	17129	O-RING in EPDM R6 7,2x1,9 mm EP851 (set of 10)

Product Number	SP Number	Long designation
179176	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
	18884	RELIEF VALVE ECOGAZ Calibrated 50 Bar for Manifold
	19329	Blind Plug for orifice Ø16x1,336 SI Brass
	19403	BLOC VALVE PURGE for Change Overs and Panels ECOGA
	175874	RELIEF VALVE ECOGAZ Body Brass / EPDM Tightness Pr
	175886	KIT SPARE REGULATOR left for Man ECOGAZ SA 200-50/
	175887	KIT SPARE REGULATOR right for Man ECOGAZ SA 200-50
155092	15970	Painemittari 0- 200/315 Bar Ø 50mm Sivusuunnassa M10x1 Brass-Cr
	17129	O-RING in EPDM R6 7,2x1,9 mm EP851 (set of 10)
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
	18546	Painemittari 0 -100 Bar Ø 50mm Takaisinsyöttö G1/4 vaihtventtiileille ECOGAZ (paitsi C2H2)
	18884	RELIEF VALVE ECOGAZ Calibrated 50 Bar for Manifold
	19329	Blind Plug for orifice Ø16x1,336 SI Brass
	19403	BLOC VALVE PURGE for Change Overs and Panels ECOGA
	64595	KIT FITTINGS ECOGAZ/M2D G3/8 BSP-G1/2BST
	151862	FLAT SEAL in PA 6.6 for GAUGE Inlet G1/4
	167800	KIT of Seals flat PA 6.6 for manometer M10x1 (2 s
	175874	RELIEF VALVE ECOGAZ Body Brass / EPDM Tightness Pr
	175886	KIT SPARE REGULATOR left for Man ECOGAZ SA 200-50/
	175887	KIT SPARE REGULATOR right for Man ECOGAZ SA 200-50
147163	15970	Painemittari 0- 200/315 Bar Ø 50mm Sivusuunnassa M10x1 Brass-Cr
	17129	O-RING in EPDM R6 7,2x1,9 mm EP851 (set of 10)
	17141	FLAT SEAL in PTCFE 14,5x10x2 for outlet port G3/8
	18546	Painemittari 0 -100 Bar Ø 50mm Takaisinsyöttö G1/4 vaihtventtiileille ECOGAZ (paitsi C2H2)
	18884	RELIEF VALVE ECOGAZ Calibrated 50 Bar for Manifold
	19329	Blind Plug for orifice Ø16x1,336 SI Brass
	19403	BLOC VALVE PURGE for Change Overs and Panels ECOGA
	64595	KIT FITTINGS ECOGAZ/M2D G3/8 BSP-G1/2BST
	151862	FLAT SEAL in PA 6.6 for GAUGE Inlet G1/4
	167800	KIT of Seals flat PA 6.6 for manometer M10x1 (2 s

Product Number	SP Number	Long designation
147163	175874	RELIEF VALVE ECOGAZ Body Brass / EPDM Tightness Pr
	175886	KIT SPARE REGULATOR left for Man ECOGAZ SA 200-50/
	175887	KIT SPARE REGULATOR right for Man ECOGAZ SA 200-50